





Expertise – Passion – Automation




## Your safety in our focus

Safety-related products  
5 port external pilot type solenoid valve  
with spring return spool  
SY-X360 Series

# 5 port external pilot type solenoid valve with spring return spool

## SY-X360 Series

- ▶ We focus on machinery safety as a key part of our product development strategy. This version will help satisfy your machine safety system requirements.



## Main features

### ▶ Spring return spool - the concept

The SY-X360 versions contain a mechanical spring return spool. In the case of pilot pressure loss, the spool moves to its de-energised position irrespective of the applied electrical control signal. When used as a safety related part of a control system, it thereby satisfies the de-energisation principle.

### ▶ Validated according to ISO 13849-2

This product is capable of meeting the relevant basic and well-tried safety principles.

Please download our reliability data for the details.


### ▶ SISTEMA library is available

SY safety-related valves data are additionally integrated into the SISTEMA software tool.

Download the library file from our website and be ready to build your safety function.

### ▶ SY series valves

Benefit from the high versatility this series gives you and create your own configuration, tailored to your needs.



## Applications

Because it has a spring to return the spool, it can be used to implement safety related control systems where the valve spool must always return to the de-energised position on loss of pilot pressure, irrespective of the applied electrical control signal.

## How to order

Base mounted SY       -    1 -  - X360

Top ported SY       -    1 -   -  - X360

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫

### ① Valve series

<b>3</b>	3000
<b>5</b>	5000
<b>7</b>	7000

### ② Type of actuation

<b>1</b>	2-position single
----------	-------------------

### ③ Seal type

<b>0</b>	Rubber seal
----------	-------------

### ④ Pilot type

<b>R</b>	External pilot
----------	----------------

### ⑤ Pilot valve option

<b>—</b>	Standard (0.7 MPa)
<b>B</b>	Quick response type (0.7 MPa)

### ⑥ Coil type

<b>—</b>	Standard
<b>T</b>	With power saving circuit (continuous duty type)

- 1) Be sure to select the power saving circuit type when the valve is continuously energized for long periods of time.
- 2) Be careful of the energizing time, as quick response and high pressure types will become operational when the energizing time is over 40 ms.

### ⑦ Rated voltage

<b>5</b>	24 VDC
<b>6</b>	12 VDC

### ⑧ Light/surge voltage suppressor and common specification

<b>—</b>	W/o indicator light & surge suppressor (non-polar)
<b>R</b>	W/surge suppressor (non-polar)
<b>U</b>	W/indicator light & surge suppressor (non-polar)
<b>S</b>	W/surge suppressor (positive common)
<b>Z</b>	W/indicator light & surge suppressor (positive common)
<b>NS</b>	W/surge suppressor (negative common)
<b>NZ</b>	W/indicator light & surge suppressor (negative common)

- 1) Only "Z" and "NZ" type is available for the product with power saving circuit.

### ⑨ Manual override

<b>—</b>	Non-locking push type
----------	-----------------------

### ⑩ A, B port size

#### Thread piping

Symbol	Port size	Applicable series
<b>M5</b>	M5 x 0.8	SY3000
<b>01</b>	1/8"	SY5000
<b>02</b>	1/4"	SY7000

#### One-touch fitting (Metric)

Symbol	A, B port	SY3000	SY5000	SY7000
<b>C2</b>	Ø 2	●	—	—
<b>C3</b>	Ø 3.2	●	—	—
<b>C4</b>	Ø 4	●	●	—
<b>C6</b>	Ø 6	●	●	●
<b>C8</b>	Ø 8	—	●	●
<b>C10</b>	Ø 10	—	—	●
<b>C12</b>	Ø 12	—	—	●

#### One-touch fitting (Inch)

Symbol	A, B port	SY3000	SY5000	SY7000
<b>N1</b>	Ø 1/8"	●	—	—
<b>N3</b>	Ø 5/32"	●	●	—
<b>N7</b>	Ø 1/4"	●	●	●
<b>N9</b>	Ø 5/16"	—	●	●
<b>N11</b>	Ø 3/8"	—	—	●

### ⑪ Thread type

<b>—</b>	Rc
<b>F</b>	G
<b>N</b>	NPT
<b>T</b>	NPTF

- 1) Only "—" is available for M5.

### ⑫ Type of mounting screw

<b>—</b>	Round head combination screw
<b>B</b>	Hexagon socket head cap screw
<b>K</b>	Round head combination screw (falling-out -prevention type)
<b>H</b>	Hexagon socket head cap screw (falling-out -prevention type)

#### Note

- \* Refer to the respective "Reliability data" for the latest "How to order".

## Valve specifications

Valve type		Rubber seal
Fluid		Air
External pilot operating pressure range [MPa]	Operating pressure range	-100 kPa to 0.7
	Pilot pressure range	0.35 to 0.7
Ambient and fluid temperature [°C]		-10 to 50 (No freezing)
Max. operating frequency [Hz]		5
Min. operating frequency		1 cycle every 30 days
Manual override		Non-locking push type
Pilot exhaust type		Pilot valve individual exhaust
Lubrication		Not required
Mounting orientation		Unrestricted
Impact/Vibration resistance <sup>1)</sup> [m/s <sup>2</sup> ]		150/30
Enclosure		IP67 (Based on IEC60529)
Coil rated voltage [VDC]		24, 12
Allowable voltage fluctuation [V]		±10 % of rated voltage <sup>2)</sup>
Power consumption [W]	Standard	0.35 (With indicator light: 0.4)
	Quick response type	0.9 (With indicator light: 0.95)
	With power saving circuit	Standard: 0.1 <sup>3)</sup> (With indicator light only) [Inrush 0.4, Holding 0.1],
Surge voltage suppressor		Diode (Varistor for non-polar type)
Indicator light		LED

1) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve and armature in both energised and de-energised states every time in each condition. (Values at the initial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. Test was performed at both energised and de-energised states in the axial direction and at right angles to the main valve and armature. (Values at the initial period)


2) Due to voltage drops by the internal circuit in S/Z type and T type (with power saving circuit), use within the allowable voltage fluctuation as follows.

$$\begin{matrix} \text{S/Z type} \\ \left\{ \begin{array}{l} 24 \text{ VDC: } -7 \% \text{ to } +10 \% \\ 12 \text{ VDC: } -4 \% \text{ to } +10 \% \end{array} \right. \end{matrix} \quad \begin{matrix} \text{T type} \\ \left\{ \begin{array}{l} 24 \text{ VDC: } -8 \% \text{ to } +10 \% \\ 12 \text{ VDC: } -6 \% \text{ to } +10 \% \end{array} \right. \end{matrix}$$

3) For technical data which are not shown in this document, please see the instruction manual or the standard catalogue at [www.smc.eu](http://www.smc.eu).

## Symbols

SY□1□□R



Note) Not all options are available for all valve sizes. Refer to "Reliability data".

## Manifold flow characteristics <sup>1) 2)</sup>

### Plug-in metal base

Series	Piping option	Port size		Valve flow-rate characteristics					
		1, 5, 3 (P, EA, EB)	4, 2 (A, B)	1→4/2 (P→A/B)			4/2→5/3 (A/B→E)		
				C [dm <sup>3</sup> /(s·bar)]	b	Q [l/min] (ANR) <sup>3)</sup>	C [dm <sup>3</sup> /(s·bar)]	b	Q [l/min] (ANR) <sup>3)</sup>
SY3000	SS5Y3-50 (Side ported)	1/8	C6	1.1	0.19	262	1.1	0.15	256
	SS5Y3-51 (Bottom ported)	1/8	C6	1.2	0.31	307	1.2	0.14	278
	SS5Y3-52 (Top ported)	1/8	C6	1.1	0.29	278	1.2	0.20	287
SY5000	SS5Y5-50 (Side ported)	1/4	C8	2.6	0.28	653	2.6	0.14	603
	SS5Y5-51 (Bottom ported)	1/4	C8	2.7	0.35	709	2.8	0.20	671
	SS5Y5-52 (Top ported)	1/4	C8	2.6	0.26	645	3.1	0.13	715
SY7000	SS5Y7-50 (Side ported)	3/8	C10	3.8	0.27	948	4.0	0.20	958
	SS5Y7-51 (Bottom ported)	3/8	C10	4.1	0.34	1070	4.8	0.20	1150
	SS5Y7-52 (Top ported)	3/8	C10	4.5	0.27	1123	4.9	0.24	1201

### Resin base

Series	Piping option	Port size		Valve flow-rate characteristics					
		1, 5, 3 (P, EA, EB)	4, 2 (A, B)	1→4/2 (P→A/B)			4/2→5/3 (A/B→E)		
				C [dm <sup>3</sup> /(s·bar)]	b	Q [l/min] (ANR) <sup>3)</sup>	C [dm <sup>3</sup> /(s·bar)]	b	Q [l/min] (ANR) <sup>3)</sup>
SY3000	SS5Y3-10 (Side ported)	C8	C6	1.4	0.30	356	1.6	0.19	381
	SS5Y3-12 (Top ported)	C8	C6	1.2	0.29	303	1.3	0.19	310
SY5000	SS5Y5-10 (Side ported)	C10	C8	3.3	0.30	839	3.6	0.17	848
	SS5Y5-11 (Bottom ported)	C10	C8		0.29	834	4.2	0.26	1042
	SS5Y5-12 (Top ported)	C10	C8	2.8	0.27	699	3.8	0.23	926
SY7000	SS5Y7-10 (Side ported)	C12	C12	6.2	0.23	1511	5.9	0.20	1413
	SS5Y7-11 (Bottom ported)	C12	C12		0.25	1529	6.6	0.21	1590
	SS5Y7-12 (Top ported)	C12	C12	5.6	0.31	1433	5.7	0.24	1397

1) The value is for manifold base with 5 stations and individually operated 2-position type.

2) These values are applicable to rubber seal type valves.

3) These values have been calculated according to ISO 6358 and indicate the flow rate under standard conditions with an inlet pressure of 0.6 MPa (relative pressure) and a pressure drop of 0.1 MPa.

## Note

For confirmation of detailed specifications and dimensions, refer to product drawings, instruction manual, reliability data and catalogue at [www.smc.eu](http://www.smc.eu).

### Other related SY products






Expertise – Passion – Automation

### SMC Corporation

Akihabara UDX 15F, 4-14-1  
Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN  
Phone: 03-5207-8249  
Fax: 03-5298-5362



<b>Austria</b>	+43 (0)2262622800	www.smc.at	office.at@smc.com
<b>Belgium</b>	+32 (0)33551464	www.smc.be	info@smc.be
<b>Bulgaria</b>	+359 (0)2807670	www.smc.bg	sales.bg@smc.com
<b>Croatia</b>	+385 (0)13707288	www.smc.hr	sales.hr@smc.com
<b>Czech Republic</b>	+420 541424611	www.smc.cz	office.at@smc.com
<b>Denmark</b>	+45 70252900	www.smc.dk.com	smc.dk@smc.com
<b>Estonia</b>	+372 651 0370	www.smcee.ee	info.ee@smc.com
<b>Finland</b>	+358 207513513	www.smc.fi	smc.fi@smc.com
<b>France</b>	+33 (0)164761000	www.smc-france.fr	supportclient.fr@smc.com
<b>Germany</b>	+49 (0)61034020	www.smc.de	info.de@smc.com
<b>Greece</b>	+30 210 2717265	www.smchellas.gr	sales@smchellas.gr
<b>Hungary</b>	+36 23513000	www.smc.hu	office.hu@smc.com
<b>Ireland</b>	+353 (0)14039000	www.smcautomation.ie	technical.ie@smc.com
<b>Italy</b>	+39 03990691	www.smcitalia.it	mailbox.it@smc.com
<b>Latvia</b>	+371 67817700	www.smc.lv	info.lv@smc.com

<b>Lithuania</b>	+370 5 2308118	www.smclt.lt	info.lt@smc.com
<b>Netherlands</b>	+31 (0)205318888	www.smc.nl	info@smc.nl
<b>Norway</b>	+47 67129020	www.smc-norge.no	post.no@smc.com
<b>Poland</b>	+48 22 344 40 00	www.smc.pl	office.pl@smc.com
<b>Portugal</b>	+351 214724500	www.smc.eu	apoiocliente.pt@smc.com
<b>Romania</b>	+40 213205111	www.smcromania.ro	office.ro@smc.com
<b>Russia</b>	+7 (812)3036600	www.smc.eu	sales@smcru.com
<b>Slovakia</b>	+421 (0)413213212	www.smc.sk	sales.sk@smc.com
<b>Slovenia</b>	+386 (0)73885412	www.smc.si	office.si@smc.com
<b>Spain</b>	+34 945184100	www.smc.eu	post.es@smc.com
<b>Sweden</b>	+46 (0)86031240	www.smc.nu	order.se@smc.com
<b>Switzerland</b>	+41 (0)523963131	www.smc.ch	helpcenter.ch@smc.com
<b>Turkey</b>	+90 212 489 0 440	www.smcturkey.com.tr	satis.tr@smc.com
<b>UK</b>	+44 (0)845 121 5122	www.smc.uk	sales.gb@smc.com

<b>South Africa</b>	+27 10 900 1233	www.smcza.co.za	Sales.za@smc.com
---------------------	-----------------	-----------------	------------------